

# Product data sheet

## Characteristics

# 8538SBG32V84CF4P21TX11

## COMBO STARTER 600VAC 18A NEMA

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\*\* : 2,837.00 USD



### Main

|                      |                             |
|----------------------|-----------------------------|
| Product              | Combination Starter         |
| Type                 | S                           |
| Control Circuit Type | Control circuit transformer |

### Complementary

|                         |  |
|-------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit<br>208 V AC 60 Hz primary circuit |
| Starter Type            | Non reversing  |
| Number of Poles         | 3P   |
| Horsepower Rating       | 3 hp 230 V AC 3 phases<br>3 hp 200 V AC 3 phases                   |
| System Voltage          | 600 V AC   |
| Control Units           | Selector switch (HAND-OFF-AUTO)                                    |
| Pilot Light             | Red indicator: on type: incandescent with push-to-test             |
| Auxiliary Contacts      | 1 NO + 1 NC  |
| Control Circuit Fusing  | 2 fuses primary circuit  |
| Thermal overload type   | Melting alloy 3 Thermal Units                                      |
| Disconnect Type         | Fusible disconnect switch, Type R Fuse, 30 A                       |
| NEMA size               | 0  |

### Environment

|                |  |
|----------------|--|
| Enclosure Type | NEMA 1 painted sheet steel and with external reset |
|----------------|--|

### Ordering and shipping details

|                       |                                    |
|-----------------------|------------------------------------|
| Category              | 21212 - 8538,39SB(NOT S*R,S*T,S*W) |
| Discount Schedule     | CP1                                |
| Nbr. of units in pkg. | 1                                  |
| Package weight(Lbs)   | 45                                 |
| Returnability         | N                                  |
| Country of origin     | MX                                 |

Contractual warranty

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---