

# Product data sheet

## Characteristics

# 8538SBG33V81CFF4P21TX11

## COMBO STARTER 600VAC 18A NEMA

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\*\* : 3,178.00 USD



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent with push-to-test
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Fusible disconnect switch, Type R Fuse, 30 A
NEMA size	0

### Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

### Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	00785901352099
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N

---

Country of origin	MX
-------------------	----

---

**Offer Sustainability**

---

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---