


Price** : 2,462.00 USD



8538SCG11V81CF4H20P21T has not been replaced.
Please contact your customer care center for more information.

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	7.5 hp 230 V AC 3 phases 10 hp 460 V AC 3 phases 10 hp 575 V AC 3 phases 7.5 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent with push-to-test
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Thermal overload type	Solid state Motor Logic class 20
Disconnect Type	Non-fusible disconnect switch
NEMA size	1

Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
