

Product data sheet

Characteristics

8538SCG13V84CF4T

COMBO STARTER 600VAC 27A NEMA

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 2,163.00 USD



Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	7.5 hp 230 V AC 3 phases 7.5 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Fusible disconnect switch, Type H Fuse, 60 A
NEMA size	1

Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901764144

Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------