




Price** : 2,163.00 USD



8538SCG34V86FF4T has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 600 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	10 hp 460 V AC 3 phases 10 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Fusible disconnect switch, Type R Fuse, 30 A
NEMA size	1

Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1

Package weight(Lbs)	45
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
