



Price\*\* : 3,551.00 USD



ⓘ Discontinued

8538SCW34V81CF4T has not been replaced. Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	10 hp 460 V AC 3 phases 10 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Fusible disconnect switch, Type R Fuse, 30 A
NEMA size	1

### Environment

Enclosure Type	NEMA 4/4X stainless steel and with external reset
----------------	---

### Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45

---

Returnability	N
---------------	---

---

**Offer Sustainability**

---

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
------------------------	--

---

---

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
-------	--

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---