



Price** : 3,380.00 USD



ⓘ Discontinued

8538SDA22V02AP1S has not been replaced. Please contact your customer care center for more information.

Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	10 hp 200 V AC, 3 phases 15 hp 230 V AC, 3 phases
Maximum Voltage Rating	600 V AC
Control Units	Push-button START) Push-button STOP)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 60 A
NEMA size	2

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

Ordering and shipping details

Discount Schedule	CP1
Package weight(Lbs)	60.00 lb(US) (27.216 kg)
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------
