

Product data sheet

Specifications



COMBO STARTER 600VAC 45A NEMA

8538SDA22V84CF4T

To be discontinued on: Sep 30, 2024

To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|----------------------|-----------------------------|
| Product | Combination Starter |
| Type | S |
| Control Circuit Type | Control circuit transformer |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit |
| Starter Type | Non reversing |
| Number Of Poles | 3P |
| Horsepower Rating | 10 hp 200 V AC, 3 phase 15 hp 230 V AC, 3 phase |
| Maximum Voltage Rating | 600 V AC |
| Control Units | Selector switch HAND-OFF-AUTO) |
| Pilot Light | No indicator |
| Auxiliary Contacts | Without |
| Control Circuit Fusing | 2 fuses primary circuit |
| Thermal Overload Type | Melting alloy 3 |
| Disconnect Type | Fusible disconnect switch H, 60 A |
| Nema Size | 2 |

Environment

| | |
|----------------|---|
| Enclosure Type | NEMA 12 painted sheet steel with external reset |
|----------------|---|

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 21213 - 8538,39 SC,SD(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|--------------------------|
| Package 1 Weight | 60.00 lb(US) (27.216 kg) |
|------------------|--------------------------|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|