

Product data sheet

Specifications



COMBO STARTER 600VAC 45A NEMA

8538SDA26V02SX10

Price*: 2,867.00 USD

⚠ Discontinued

Main

| | |
|----------------------|--------------------------|
| Product | Combination Starter |
| Type | S |
| Control Circuit Type | Separate control circuit |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 110 V AC 50 Hz 120 V AC 60 Hz |
| Starter Type | Non reversing |
| Number Of Poles | 3P |
| Horsepower Rating | 15 hp 460 V AC, 3 phase 15 hp 575 V AC, 3 phase |
| Maximum Voltage Rating | 600 V AC |
| Control Units | No control units |
| Pilot Light | No indicator |
| Auxiliary Contacts | 1 NO |
| Thermal Overload Type | Melting alloy 3 |
| Disconnect Type | Fusible disconnect switch H, 30 A |
| Nema Size | 2 |

Environment

| | |
|----------------|---|
| Enclosure Type | NEMA 12 painted sheet steel with external reset |
|----------------|---|

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |

Packing Units

| | |
|------------------------------|--------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 60.00 lb(US) (27.216 kg) |

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months