

Price** : 3,824.00 USD



8538SDG11V81CFF4P21TX10 has not been replaced.
Please contact your customer care center for more information.

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	15 hp 230 V AC 3 phases 25 hp 575 V AC 3 phases 25 hp 460 V AC 3 phases 10 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent with push-to-test
Auxiliary Contacts	1 NO
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Non-fusible disconnect switch
NEMA size	2

Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	37.200000000000003
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
