

Price\*\* : 3,455.00 USD



8538SDG11V83CFF4H20TX10 has not been replaced.  
Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	240 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	15 hp 230 V AC 3 phases 25 hp 575 V AC 3 phases 25 hp 460 V AC 3 phases 10 hp 200 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	1 NO
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Solid state Motor Logic class 20
Disconnect Type	Non-fusible disconnect switch
NEMA size	2

### Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
----------------	--

### Ordering and shipping details

Category	21214 - 8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	42.35999999999999
Returnability	N

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---