

Price** : 6,228.00 USD



8538SDW36V81AF4F10P1P2TX01 has not been replaced.
Please contact your customer care center for more information.

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	15 hp 460 V AC 3 phases 15 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Push-button (START) Push-button (STOP)
Pilot Light	Red indicator: on type: incandescent Green indicator: off type: incandescent
Auxiliary Contacts	1 NC
Control Circuit Fusing	2 fuses primary circuit 2 fuses secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Fusible disconnect switch, Type R Fuse, 30 A
NEMA size	2

Environment

Enclosure Type	NEMA 4/4X stainless steel and with external reset
----------------	---------------------------------------------------

Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	60
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
