

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 45A NEMA

8538SEA21V81C6FF4P1T11X11

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	25 hp 200 V AC, 3 phase 30 hp 230 V AC, 3 phase 50 hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch ON-OFF)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal Overload Type	Melting alloy 3
Disconnect Type	Non-fusible disconnect switch
Nema Size	3

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

Ordering and shipping details

Category	21214-8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications