

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 45A NEMA

8539SDW51V06C

! Discontinued

Main

Circuit Breaker Type	GJL36015M03
Contactor Application	Non-reversing
Device Short Name	S

Complementary

Depth	11.4 in (289.56 mm)
Device Mounting	Surface
Height	27 in (685.80 mm)
Maximum Horse Power Rating	1.5...3 hp 200/230 V AC 5...7.5 hp 460 V AC 5...10 hp 575 V AC
Nema Size	2
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker GJL36015M03
Net Weight	55 lb(US) (24.95 kg)
Width	25.25 in (641.35 mm)

Environment

Nema Degree Of Protection	NEMA 4X
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21217-8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	60.00 lb(US) (27.216 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------