

Price\* : 7,745.00 USD



8539SDW53V81AFF4P1P2TX22 has not been replaced.  
Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	10 hp 230 V AC 3 phases 25 hp 575 V AC 3 phases 7.5...10 hp 200 V AC 3 phases 20...25 hp 460 V AC 3 phases
System Voltage	600 V AC
Control Units	Push-button (START) Push-button (STOP)
Pilot Light	Red indicator: on type: incandescent Green indicator: off type: incandescent
Auxiliary Contacts	2 NO + 2 NC
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Mag-Gard circuit breaker

### Environment

Enclosure Type	NEMA 4X glass polyester and with external reset
NEMA size	2

### Ordering and shipping details

Category	21217 - 8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	60

---

Returnability	N
---------------	---

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---