

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 90A NEMA

8539SEG42V07C

! Discontinued

Main

| | |
|----------------------|------------------------|
| Product | Combination Starter |
| Type | S |
| Control Circuit Type | Common control circuit |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 550 V AC 50 Hz 600 V AC 60 Hz |
| Starter Type | Non reversing |
| Number Of Poles | 3P |
| Horsepower Rating | 15...25 hp 200 V AC, 3 phase 15...30 hp 230 V AC, 3 phase 30...50 hp 460 V AC, 3 phase 40...50 hp 575 V AC, 3 phase |
| Maximum Voltage Rating | 600 V AC |
| Control Units | Selector switch HAND-OFF-AUTO) |
| Pilot Light | No indicator |
| Auxiliary Contacts | Without |
| Thermal Overload Type | Melting alloy 3 |
| Disconnect Type | Mag-Gard circuit breaker |

Environment

| | |
|----------------|--|
| Enclosure Type | NEMA 1 painted sheet steel with external reset |
| Nema Size | 3 |

Ordering and shipping details

| | |
|-------------------|----------------------------------|
| Category | 21214-8538,39 SE,SF(NOT S*R,T,W) |
| Discount Schedule | CP1 |
| Returnability | No |

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 107.00 lb(US) (48.534 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|