



Price* : 3,879.00 USD



8539SEG42V08 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Contacteur application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure standard environment indoor

Complementary

Rated current	90 A
System Voltage	208 V AC 60 Hz
Depth	10.59 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	42 in
Motor power hp	15...25 hp 200 V AC 15...30 hp 230 V AC 30...50 hp 460 V AC 40...50 hp 575 V AC
NEMA size	3
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker FAL3610018M
Product weight	102 lb(US)
Short-circuit protection	22000 A AIR
Thermal overload type	Melting alloy
Width	15.25 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21214 - 8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	102
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------