


Price* : 5,688.00 USD



8539SEG42V84AF4P1TX30 has not been replaced.
Please contact your customer care center for more information.

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz 208 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	15...25 hp 200 V AC 3 phases 15...30 hp 230 V AC 3 phases 30...50 hp 460 V AC 3 phases 40...50 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Push-button (START) Push-button (STOP)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	3 NO
Control Circuit Fusing	2 fuses primary circuit
Thermal overload type	Melting alloy
Disconnect Type	Mag-Gard circuit breaker

Environment

Enclosure Type	NEMA 1 painted sheet steel and with external reset
NEMA size	3

Ordering and shipping details

Category	21214 - 8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	107
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
