



Price* : 9,278.00 USD

8539SER42V08C has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	15...25 hp 200 V AC 3 phases 15...30 hp 230 V AC 3 phases 30...50 hp 460 V AC 3 phases 40...50 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Mag-Gard circuit breaker

Environment

Enclosure Type	NEMA 7/9 cast aluminium spin top and with external reset
NEMA size	3

Ordering and shipping details

Category	21217 - 8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	145

Returnability	N
---------------	---

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
