



Price* : 10,629.00 USD



8539SER6V81AFF4T has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	30 hp 460 V AC 3 phases 40 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Push-button (START) Push-button (STOP)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Thermal magnetic circuit breaker 80 A

Environment

Enclosure Type	NEMA 7/9 cast aluminium spin top and with external reset
NEMA size	3

Ordering and shipping details

Category	21217 - 8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1

Package weight(Lbs)	145
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
