

# Product data sheet

Specifications



## OBSOLETE COMBINATION STARTER

8539SET1V03

! Discontinued

### Main

|                      |                        |
|----------------------|------------------------|
| Product              | Combination Starter    |
| Type                 | S                      |
| Control Circuit Type | Common control circuit |

### Complementary

|                         |                                                                               |
|-------------------------|-------------------------------------------------------------------------------|
| Control Circuit Voltage | 220 V AC 50 Hz<br>240 V AC 60 Hz                                              |
| Starter Type            | Non reversing                                                                 |
| Number Of Poles         | 3P                                                                            |
| Horsepower Rating       | 20 hp 200 V AC, 3 phase<br>25 hp 230 V AC, 3 phase<br>50 hp 460 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC                                                                      |
| Control Units           | No control units                                                              |
| Pilot Light             | No indicator                                                                  |
| Auxiliary Contacts      | Without                                                                       |
| Thermal Overload Type   | Melting alloy 3                                                               |
| Disconnect Type         | Thermal magnetic circuit breaker, 100 A                                       |

### Environment

|                |                                                    |
|----------------|----------------------------------------------------|
| Enclosure Type | NEMA 7/9 Cast Aluminium bolted with external reset |
| Nema Size      | 3                                                  |

### Ordering and shipping details

|                   |                           |
|-------------------|---------------------------|
| Category          | 21217-8538,39 S*R,S*T,S*W |
| Discount Schedule | CP1                       |
| Returnability     | No                        |

### Packing Units

|                              |                           |
|------------------------------|---------------------------|
| Unit Type Of Package 1       | PCE                       |
| Number Of Units In Package 1 | 1                         |
| Package 1 Weight             | 180.00 lb(US) (81.647 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|