

Product data sheet

Specifications



OBSOLETE COMBINATION STARTER

8539SET3V06

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	15 hp 200 V AC, 3 phase 20 hp 230 V AC, 3 phase 40 hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal Overload Type	Melting alloy 3
Disconnect Type	Thermal magnetic circuit breaker, 90 A

Environment

Enclosure Type	NEMA 7/9 Cast Aluminium bolted with external reset
Nema Size	3

Ordering and shipping details

Category	21217-8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	180.00 lb(US) (81.647 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------