

Product data sheet

Specifications



OBSOLETE COMBINATION STARTER

8539SET41V07C

Price*: 9,278.00 USD

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	550 V AC 50 Hz 600 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	20...25 hp 460 V AC, 3 phase 25...30 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal Overload Type	Melting alloy 3
Disconnect Type	Mag-Gard circuit breaker

Environment

Enclosure Type	NEMA 7/9 Cast Aluminium bolted with external reset
Nema Size	3

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	185.00 lb(US) (83.915 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months