



Price\* : 8,679.00 USD



8539SET42V02S has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Contacteur application	Non-reversing
Control circuit	Separate control circuit
Device short name	S
Disconnecteur device type	Mag-Gard circuit breaker
Enclosure type	Bolted hazardous location indoor

### Complementary

Rated current	90 A
System Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Depth	10 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Cast aluminium
Height	31.63 in
Motor power hp	15...25 hp 200 V AC 15...30 hp 230 V AC 30...50 hp 460 V AC 40...50 hp 575 V AC
NEMA size	3
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker FAL3610018M
Product weight	180 lb(US)
Short-circuit protection	5000 A AIR
Thermal overload type	Melting alloy
Width	18.06 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

NEMA degree of protection	NEMA 7/9
---------------------------	----------

## Ordering and shipping details

Category	21217 - 8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	185
Returnability	N

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------