




Price* : 7,554.00 USD



ⓘ Discontinued

8539SEW1V06 has not been replaced. Please contact your customer care center for more information.

Main

Contactors application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnectors device type	Thermal magnetic circuit breaker 100 A
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor Enclosure corrosion resistance indoor/outdoor

Complementary

Rated current	90 A
System Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Depth	10.59 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Brushed stainless steel
Height	42 in
Motor power hp	20 hp 200 V AC 25 hp 230 V AC 50 hp 480 V AC
NEMA size	3
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker FAL
Product weight	111 lb(US)
Short-circuit protection	5000 A AIR
Thermal overload type	Melting alloy
Width	15.25 in

Environment

NEMA degree of protection	NEMA 4/4X
Product certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	111
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------