

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 7,554.00 USD



### Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	40 hp 460 V AC 3 phases 50 hp 575 V AC 3 phases 15 hp 200 V AC 3 phases 20 hp 230 V AC 3 phases
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Thermal magnetic circuit breaker 90 A

### Environment

Enclosure Type	NEMA 4/4X brushed stainless steel and with external reset
NEMA size	3

### Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1

Nbr. of units in pkg.	1
Package weight(Lbs)	111
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

**Contractual warranty**

Warranty period	18 months
-----------------	-----------