

# Product data sheet

Specifications

SQUARE D



## COMBO STARTER 600VAC 90A NEMA

8539SEW42V03C

Discontinued

### Main

|                      |                        |
|----------------------|------------------------|
| Product              | Combination Starter    |
| Type                 | S                      |
| Control Circuit Type | Common control circuit |

### Complementary

|                         |                                                                                                                              |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Control Circuit Voltage | 220 V AC 50 Hz<br>240 V AC 60 Hz                                                                                             |
| Starter Type            | Non reversing                                                                                                                |
| Number Of Poles         | 3P                                                                                                                           |
| Horsepower Rating       | 15...25 hp 200 V AC, 3 phase<br>15...30 hp 230 V AC, 3 phase<br>30...50 hp 460 V AC, 3 phase<br>40...50 hp 575 V AC, 3 phase |
| Maximum Voltage Rating  | 600 V AC                                                                                                                     |
| Control Units           | Selector switch HAND-OFF-AUTO)                                                                                               |
| Pilot Light             | No indicator                                                                                                                 |
| Auxiliary Contacts      | Without                                                                                                                      |
| Thermal Overload Type   | Melting alloy 3                                                                                                              |
| Disconnect Type         | Mag-Gard circuit breaker                                                                                                     |

### Environment

|                |                                                       |
|----------------|-------------------------------------------------------|
| Enclosure Type | NEMA 4/4X brushed stainless steel with external reset |
| Nema Size      | 3                                                     |

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21218-8538,39 W/STAINLESS ENCLOS |
| Discount Schedule | CP1                              |
| Returnability     | No                               |

### Packing Units

|                              |                           |
|------------------------------|---------------------------|
| Unit Type Of Package 1       | PCE                       |
| Number Of Units In Package 1 | 1                         |
| Package 1 Weight             | 116.00 lb(US) (52.617 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|