

# Product data sheet

Specifications

SQUARE D



## COMBO STARTER 600VAC 90A NEMA

8539SEW52V02AH20P2S

! Discontinued

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	15...25 hp 200 V AC, 3 phase 15...30 hp 230 V AC, 3 phase 30...50 hp 460 V AC, 3 phase 40...50 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Push-button START) Push-button STOP)
Pilot Light	Green indicator off incandescent
Auxiliary Contacts	Without
Thermal Overload Type	Solid state Motor Logic class 20
Disconnect Type	Mag-Gard circuit breaker

### Environment

Enclosure Type	NEMA 4X glass polyester with external reset
Nema Size	3

### Ordering and shipping details

Category	21217-8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications