

Product data sheet

Specifications

SQUARE D



COMBO STARTER 600VAC 135A NEMA

8539SFA11V07

! Discontinued

Main

Circuit Breaker Type	KAL
Contactor Application	Non-reversing
Device Short Name	S
Disconnecter Device Type	Thermal magnetic circuit breaker 150 A

Complementary

Rated Current	135 A
[Ue] Rated Operational Voltage	600 V AC 60 Hz 550 V AC 50 Hz
Depth	10.53 in (267.46 mm)
Device Mounting	Surface
Height	52.5 in (1333.50 mm)
Maximum Horse Power Rating	40 hp 230 V AC 100 hp 575 V AC
Nema Size	4
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker KAL
Net Weight	170 lb(US) (77.11 kg)
Reset	With external
Short-Circuit Protection	10000 A AIR
Width	16 in (406.40 mm)

Environment

Nema Degree Of Protection	NEMA 12
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21214-8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	170.00 lb(US) (77.111 kg)

Contractual warranty

Warranty	18 months
----------	-----------