




Price* : 10,245.00 USD



8539SFA42V06 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Contacteur application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure dust and damp proof indoor

Complementary

Rated current	135 A
System Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Depth	10.53 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	52.5 in
Motor power hp	30 hp 200 V AC 60...75 hp 460 V AC 60...100 hp 575 V AC
NEMA size	4
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker KAL3625025M
Product weight	170 lb(US)
Reset	Without external
Short-circuit protection	22000 A AIR
Thermal overload type	Melting alloy
Width	16 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

NEMA degree of protection	NEMA 12
Product certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21214 - 8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	170
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------