


Price\* : 11,613.00 USD



8539SFA54V81AF4H20T has not been replaced. Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	30...40 hp 200 V AC 3 phases 40...50 hp 230 V AC 3 phases 60...100 hp 460 V AC 3 phases 60...100 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	Push-button (START) Push-button (STOP)
Pilot Light	No indicator
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Thermal overload type	Solid state Motor Logic class 20
Disconnect Type	Mag-Gard circuit breaker

### Environment

Enclosure Type	NEMA 12 painted sheet steel and with external reset
NEMA size	4

### Ordering and shipping details

Category	21214 - 8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	175
Returnability	N

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---