



Price\* : 13,521.00 USD



ⓘ Discontinued

8539SFT43V08 has not been replaced. Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	208 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	40 hp 200 V AC 3 phases 40 hp 230 V AC 3 phases
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Mag-Gard circuit breaker

### Environment

Enclosure Type	NEMA 7/9 cast aluminium bolted and with external reset
NEMA size	4

### Ordering and shipping details

Category	21217 - 8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	180
Returnability	N

Offer Sustainability

---

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

---

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---