




Price* : 14,534.00 USD



8539SFW11V03 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Circuit breaker type	KAL
Contactor application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Thermal magnetic circuit breaker 150 A
Enclosure type	Enclosure water resistant Enclosure dustproof Enclosure corrosion resistance

Complementary

Rated current	135 A
System Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Depth	11.4 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Glass polyester
Height	33.5 in
Motor power hp	40 hp 230 V AC 100 hp 575 V AC
NEMA size	4
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker KAL
Product weight	120 lb(US)
Short-circuit protection	10000 A AIR
Thermal overload type	Melting alloy

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	26.31 in
-------	----------

Environment

NEMA degree of protection	NEMA 4X
Product certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21217 - 8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	120
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
