

Product data sheet

Specifications

SQUARE D



COMBINATION STARTER

8539SFW4V80AF4TX12

Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz 240 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	40 hp 200 V AC, 3 phase 50 hp 230 V AC, 3 phase 100 hp 460 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Push-button START) Push-button STOP)
Pilot Light	No indicator
Auxiliary Contacts	1 NO + 2 NC
Control Circuit Fusing	2 fuses primary circuit
Thermal Overload Type	Melting alloy 3
Disconnect Type	Thermal magnetic circuit breaker, 200 A

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel with external reset
Nema Size	4

Ordering and shipping details

Category	21218-8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	142.00 lb(US) (64.41 kg)
------------------	--------------------------

Contractual warranty

Warranty	18 months
----------	-----------