

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 22,859.00 USD



Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	100 hp 230 V AC 3 phases 200 hp 460 V AC 3 phases
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Mag-Gard circuit breaker

Environment

Enclosure Type	NEMA 12 painted sheet steel and without external reset
NEMA size	5

Ordering and shipping details

Category	21215 - 8538,39SG(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	440

Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	------------------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
