

# Product data sheet

Specifications

SQUARE D



## COMBO STARTER 600VAC 270A NEMA

8539SGT4V08

⚠ Discontinued on: Nov 11, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	208 V AC 60 Hz
Starter Type	Non reversing
Number Of Poles	3P
Horsepower Rating	75 hp 200 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal Overload Type	Melting alloy 3
Disconnect Type	Thermal magnetic circuit breaker, 300 A

### Environment

Enclosure Type	NEMA 7/9 Cast Aluminium bolted with external reset
Nema Size	5

### Ordering and shipping details

Category	21217-8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>