

# Product data sheet

Specifications

SQUARE D



## COMBO STARTER 600VAC 540A NEMA

8539SHG4V03

! Discontinued

### Main

Contactor Application	Non-reversing
Device Short Name	S
Disconnecter Device Type	Thermal magnetic circuit breaker 450 A

### Complementary

Rated Current	540 A
Depth	21.03 in (534.16 mm)
Device Mounting	Surface
Height	90 in (2286.00 mm)
Maximum Horse Power Rating	100 hp 200 V AC 125 hp 230 V AC 250 hp 460 V AC 300 hp 575 V AC
Nema Size	6
Number Of Poles	3
Number Of Thermal Units Required	3
Product Destination	Circuit breaker MAL
Short-Circuit Protection	18000 A AIR
Width	36 in (914.40 mm)

### Environment

Nema Degree Of Protection	NEMA 1
Product Certifications	UL listed file E152395 CCN NKJH7

### Ordering and shipping details

Category	21216-8538,39 SH,SJ(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	440.00 lb(US) (199.581 kg)

## Contractual warranty

Warranty	18 months
----------	-----------