

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 49,946.00 USD



Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	600 V AC 60 Hz 550 V AC 50 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	250 hp 575 V AC 3 phases
System Voltage	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnect Type	Mag-Gard circuit breaker

Environment

Enclosure Type	NEMA 4 painted sheet steel and with external reset
NEMA size	6

Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	440
Returnability	Y

Country of origin	MX
-------------------	----

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
