

# Product data sheet

Specifications

SQUARE D



NEMA Combination Starter, Type S, 1200A PKL thermal magnetic circuit breaker, Size 7, 810A, 3 phase, 240VAC coil, NEMA 1

8539SJG2V03

! To be discontinued

! To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

|                      |                        |
|----------------------|------------------------|
| Product              | Combination Starter    |
| Type                 | S                      |
| Control Circuit Type | Common control circuit |

## Complementary

|                         |   |
|-------------------------|---|
| Control Circuit Voltage | 220 V AC 50 Hz<br>240 V AC 60 Hz        |
| Starter Type            | Non reversing                           |
| Number Of Poles         | 3P                                      |
| Horsepower Rating       | 500...600 hp 575 V AC, 3 phase          |
| Maximum Voltage Rating  | 600 V AC                                |
| Control Units           | No control units                        |
| Pilot Light             | No indicator                            |
| Auxiliary Contacts      | Without                                 |
| Thermal Overload Type   | Melting alloy 3                         |
| Disconnect Type         | Thermal magnetic circuit breaker, 900 A |

## Environment

|                |  |
|----------------|--|
| Enclosure Type | NEMA 1 painted sheet steel with external reset |
| Nema Size      | 7  |

## Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 21216 - 8538,39 SH,SJ(NOT S*R,T,W) |
| Discount Schedule | CP1                                |
| Returnability     | No                                 |
| Country Of Origin | MX                                 |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |                            |
|------------------|----------------------------|
| Package 1 Weight | 700.00 lb(US) (317.515 kg) |
|------------------|----------------------------|

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

|                           |   |
|---------------------------|---|
| Eu Rohs Directive         | Not compliant   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |