

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 10,260.80 USD



Main

Control circuit	Separate control circuit
Device short name	S
Enclosure type	Enclosure standard environment indoor

Complementary

Rated current	45 A
System Voltage	480 V AC
[Uc] control circuit voltage	120 V AC
Depth	9.38 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	50 in
Motor power hp	25 hp
NEMA size	2
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product weight	250 lb(US)
Thermal overload type	Melting alloy
Width	25 in

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E70074 CCN NLDX

Ordering and shipping details

Category	21231 - 8606 (NOT S*K)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	500
Returnability	N
Country of origin	MX