

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 9,519.40 USD



Main

Control circuit	Separate control circuit
Device short name	S
Product specific application	OEM applications

Complementary

Rated current	90 A
System Voltage	600 V AC
[Uc] control circuit voltage	120 V AC
Electrical connection	Screw clamp terminal
Motor power hp	30 hp
NEMA size	3
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Thermal overload type	Melting alloy

Environment

Product certifications	UL listed file E70074 CCN NLDX
------------------------	--------------------------------

Ordering and shipping details

Category	21232 - 8606 S*K OEM KITS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	250
Returnability	N

Country of origin	MX
-------------------	----
