

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 18,421.00 USD



### Main

Control circuit	Separate control circuit
Device short name	S
Product specific application	OEM applications

### Complementary

Rated current	135 A
System Voltage	600 V AC
[Uc] control circuit voltage	120 V AC
Electrical connection	Screw clamp terminal
Motor power hp	100 hp
NEMA size	4
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Thermal overload type	Melting alloy

### Environment

Product certifications	UL listed file E70074 CCN NLDX
------------------------	--------------------------------

### Ordering and shipping details

Category	21232 - 8606 S*K OEM KITS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	325
Returnability	N

---

Country of origin	MX
-------------------	----

---

**Offer Sustainability**

---

RoHS (date code: YYWW)	Will not be compliant
	Will not be compliant

---