

Product data sheet

Specifications

SQUARE D



AUTOTRFMR STARTER 600VAC 135AMP

8606SFW1JV03

 To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

 To be discontinued

Main

Device Short Name	S
-------------------	---

Complementary

Rated Current	135 A
[Ue] Rated Operational Voltage	240 V AC
[Uc] Control Circuit Voltage	240 V AC
Depth	16 in (406.40 mm)
Device Mounting	Surface
Height	75 in (1905.00 mm)
Maximum Horse Power Rating	50 hp
Nema Size	4
Number Of Poles	3
Number Of Thermal Units Required	3
Net Weight	560 lb(US) (254.01 kg)
Width	32 in (812.80 mm)

Environment

Nema Degree Of Protection	NEMA 4
Product Certifications	UL listed file E70074 CCN NLDX

Ordering and shipping details

Category	21231 - 8606 (NOT S*K)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	75.00 in (190.5 cm)
Package 1 Width	32.01 in (81.3 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	15.98 in (40.6 cm)
Package 1 Weight	550.00 lb(US) (249.476 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
-------------------	---------------
