

Product data sheet

Specifications



AUTOTRFMR STARTER 600VAC 270AMP

8606SGK1PV81S

To be discontinued on: Sep 30, 2024

To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device Short Name	S
Product Specific Application	OEM applications

Complementary

Rated Current	270 A
[Ue] Rated Operational Voltage	480 V AC
[Uc] Control Circuit Voltage	120 V AC
Maximum Horse Power Rating	150 hp
Nema Size	5
Number Of Poles	3
Number Of Thermal Units Required	3

Environment

Product Certifications	UL listed file E70074 CCN NLDX
------------------------	--------------------------------

Ordering and shipping details

Category	21232 - 8606 S*K OEM KITS
Discount Schedule	CP1
Gtin	785901885078
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	340.00 lb(US) (154.221 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.