

Product data sheet

Specifications

SQUARE D



REVERSING CONTACTOR 240VAC 9A NEMA

8702SAG1V02S

! Discontinued

Main

Device Short Name	S
-------------------	---

Complementary

Line Rated Current	9 A
Depth	7.41 in (188.21 mm)
Device Mounting	Surface
Height	11.88 in (301.75 mm)
Maximum Horse Power Rating	0.34 hp 115 V AC 1 hp 230 V AC
Nema Size	00
Number Of Poles	2
Net Weight	16 lb(US) (7.26 kg)
Width	11.88 in (301.75 mm)

Environment

Nema Degree Of Protection	NEMA 1
Product Certifications	UL listed file E78351 CCN NLDX CSA LR60905 class 3211 04

Ordering and shipping details

Category	21271-8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	21.91 lb(US) (9.938 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications