

8702SAG4V06C14

Reversing Contactor, Size 00, 3-Pole, NEMA 1 +Options



Price* : 1,251.00 USD



8702SAG4V06C14 has not been replaced. Please contact your customer care center for more information.

Main

Product	Contactator
Type	Type S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Contactor Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	9 A
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	Selector switch (FORWARD-OFF-REVERSE)
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
NEMA size	00
Height	11.89 in (302 mm)
Depth	7.4 in (188 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	50
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------