

Product data sheet

Specifications

SQUARE D



Reversing Contactor, Size 00, 3-Pole, NEMA 1 +Options

8702SAG4V06C14

Price*: 1,251.00 USD

! Discontinued

Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

Complementary

Nema Size	00
Rated Current	9 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	Selector switch (FORWARD-OFF-REVERSE)
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	11.89 in (302 mm)
Width	11.89 in (302 mm)
Depth	7.40 in (188 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	50.00 lb(US) (22.68 kg)

Contractual warranty

Warranty	18 months
----------	-----------