

8702SAO4V11S

Reversing Contactor, Size 00, 3-Pole, Horizontal Open Style +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 855.00 USD



Main

Product	Contacteur
Type	Type S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	12 V AC 60 Hz
Contacteur Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	9 A
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
NEMA size	00
Height	5 in (127 mm)
Depth	5.31 in (135 mm)
Width	7.13 in (181 mm)

Environment

Enclosure Type	Not rated (open device)
Orientation	Horizontal

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	Y

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
