

8702SBG1V82F4T

Reversing Contactor, Size 0, 2-Pole, NEMA 1 +Options



Price* : 1,443.00 USD



8702SBG1V82F4T has not been replaced. Please contact your customer care center for more information.

Main

Product	Contactator
Type	Type S
Control Circuit Type	Control circuit transformer

Complementary

Control Circuit Voltage	240 V (primary), 24 V (secondary)
Contactator Type	Reversing
Number of Poles	2P
Phase	1 phase
Motor Wiring	3 wires
Line Rated Current	18 A
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
NEMA size	0
Height	11.89 in (302 mm)
Depth	7.4 in (188 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	25.82
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------