

Product data sheet

Specifications

SQUARE D



Reversing Contactor, Size 0, 3-Pole, NEMA 1 +Options

8702SBG4V84F4T11

Price*: 1,772.00 USD

! Discontinued

Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Coil Voltage	208 V (primary), 120 V (secondary)
Control Circuit Type	Control circuit transformer
Control Units	No control units
Other Equipment	2 fuses (primary)
Terminal Type	Screw clamp terminals
Height	11.89 in (302 mm)
Width	11.89 in (302 mm)
Depth	7.40 in (188 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA UL Listed

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	25.82 lb(US) (11.712 kg)

Contractual warranty

Warranty	18 months
----------	-----------